



Differential HCSSL Clock Oscillator, no PLL
CXO7050CK 2.5, 2.5V, 200 fsec Jitter

- SMD in ceramic case (7.0 x 5.0 x 1.8) mm
- Tri-State Enable / Disable on pad No. 1
- Fem to second integrated phase jitter (200 fs typical, 12 KHz to 20 MHz)
- Superior phase noise (-138 dBc/Hz at 10 KHz and -144 dBc/Hz at 100 KHz offset)
- RoHS conform; Lead-free product; on Tape (16mm) & Reel
- Vibration: MIL-STD-202F method 204, 35G, 50 to 2000 Hz
- Shock: MIL-STD-202F method 213B, test cond. E, 1000GG 1/2 sine wave
- High performance with surprisingly low price



Specifications

Holder Type:	CXO7050CK 2.5; 2.5V (Voltage code is "2.5"); Tri-State on pad 1
Frequency:	125.000000 MHz
Frequency Stability at 25°C:	± 25.0 ppm
Operating Temperature Range:	± 25.0 ppm over -40°C to +85°C (inclusive of 25°C tolerance, ± 10% input voltage variation, load change, aging, shock and vibration)
Storage Temperature:	-55°C to +150°C
Power Supply Voltage (Vdd):	+ 2.5V D.C. ± 5%
Maximum Supply Current (15pF load):	25.0 mA max.
Output Swing:	620 mV min; 700 mV typical; 780 mV max.
Output Logic Levels:	High "1" Voh 660 mV min.; 740 mV typical; 850 mV max. Low "0" Vol -150 mV min.; 0 mV typical; 150 mV max.
Output Symmetry (Duty Cycle):	50% ± 5% max. measured at Q and complimentary Q cross point
Load:	RL = 500ohm to ground on each output
Rise/Fall Time:	0.15 ns. typ; 0.4 ns. max. 20% -> 80% of HCSSL waveform/(RL = 100 , CL = 10pF)
Start Up Time:	3 ms typical; 10 ms max.
Tri-state Function Pin 1:	If not connected or 2.4V min. (referenced to ground) is applied: Output. Internal pull-up. Oscillation disable time is 0.2 µs max. If 0.6V max. is applied: High impedance. Current consumption is 10 µA max. Oscillation enable time is 2ms. max.
Phase Jitter (12 kHz to 20 MHz):	200 fs typical for 155.52 MHz
Phase Noise (125 MHz):	-50dBc/Hz @ 10Hz, -82dBc/Hz @ 100Hz, -116dBc/Hz @ 1kHz -138dBc/Hz @ 10kHz, -144dBc/Hz @ 100kHz, -149dBc/Hz @ 1MHz, -155dBc/Hz @ 10MHz
Aging:	< ± 3ppm max. for the first year
Reflow Condition:	260°C max for 10 sec.

GERMANY:

COMTEC CRYSTALS GmbH · Sultenstrasse 12-14
8 5 5 8 6 P o i n g / G E R M A N Y
Phone +49 8121 778160 · Fax +49 8121 778177
e-Mail info@comtec-crystals.com
Internet: <http://www.comtec-crystals.com>
Subject to change without prior notice.



Technical Data and Graphics are all under
Copyright (c) of Comtec Crystals Group.

FRANCE:

COMTEC CRYSTALS SARL · 23, rue du Faucon
6 7 5 0 0 H a g u e n a u / F R A N C E
Phone +33 388 732162 · Fax +33 388 730118
e-Mail sales@comtec-crystals.com
Internet: <http://www.comtec-crystals.com>
Sous réserve de modifications.